



RLKW12-50CPR

1/2" RADIAFLEX® RLKW Cable, A-series



- RADIAFLEX® functions as a distributed antenna to provide communications in tunnels, mines and large building complexes and is the solution for any application in confined areas.
- Slots in the copper outer conductor allow a controlled portion of the internal RF energy to be radiated into the surrounding environment. Conversely, a signal transmitted near the cable will couple into the slots and be carried along the cable length.
- RADIAFLEX® is used for both one-way and two-way communication systems and because of its broadband capability, a single radiating cable can handle multiple communication systems simultaneously.
- This RADIAFLEX® radiating cable utilize a low-loss cellular polyethylene foam dielectric and a smooth copper outer conductor which offers a superior electrical performance together with good bending properties.

Feature / Benefits

- Wideband from 30 MHz to 1950 MHz
- For applications in tunnels and buildings
- Low coupling loss variations

Technical features

GENERAL SPECIFICATIONS

Size	1/2
------	-----

ELECTRICAL SPECIFICATIONS

Max. Operating Frequency	1950 MHz
Cable Type	RLKW
Impedance	50 +/- 2
Velocity	88 percent
Capacitance	76pF/m (23.2pF/ft)
Inductance	0.19µH/m (0.058µH/ft)
DC-resistance inner conductor	1.97ohm/1000 m (0.6ohm/1000 ft)
DC-resistance outer conductor	4.84ohm/1000 m (1.48ohm/1000 ft)
Stop bands	115-135, 235-255, 360-375, 475-505, 600-630, 720-750, 970-1075, 1340-1460, 1590-1700
Frequency Selection	600, 900, 1800/1900

**RLKW12-50CPR**

1/2" RADIAFLEX® RLKW Cable, A-series

MECHANICAL SPECIFICATIONS

Jacket	CPR, EN50575:2014 + A1:2016 classified cable
Jacket Description	Halogen free, non corrosive, flame and fire retardant, low smoke, polyolefin + flame barrier tape above outer conductor for lowest cable loss
Slot Design	Groups of vertical slots at short intervals
Inner Conductor Material	Copper Clad Aluminum Wire
Outer Conductor Material	Overlapping Copper Foil
Diameter Inner Conductor	4.4mm (0.17in)
Diameter Outer Conductor	11.4mm (0.45in)
Minimum Bending Radius	200mm (7.9in)
Cable Weight	0.23kg/m (0.16lb/ft)
Tensile Force	1300N (292lb)
Indication of Slot Alignment	Bulge atop slots
Recommended / Maximum Clamp Spacing	0.5m (1.6ft)
Minimum Distance to Wall	80mm (3.15in)

TESTING AND ENVIRONMENTAL

Jacket Testing Methods	Test methods for fire behaviour of cable : IEC 60754-1/-2 smoke emission: halogen free, non corrosive IEC 61034 low smoke IEC 60332-1 flame retardant IEC 60332-3-24 fire retardant UL1666, ASTM E 662, NES711 and NES713 CPR: EN50575:2017 class B2ca s1a d0 a1
------------------------	--

TEMPERATURE SPECIFICATIONS

Storage Temperature	-70°C to 85°C (-94°F to 185°F)
Installation Temperature	-15°C to 60°C (5°F to 140°F)
Operation Temperature	-40°C to 85°C (-40°F to 185°F)

ATTENUATION AND POWER RATING

Frequency, MHz	Longitudinal Loss, dB/100 m (dB/100 ft)	Coupling Loss 50%, dB	Coupling Loss 95%, dB
75	2,17 (0,66)	45 (49)	56 (60)
150	3,10 (0,94)	58 (58)	64 (67)
450	5,74 (1,75)	58 (62)	62 (66)
800	7,89 (2,40)	61 (62)	63 (66)
870	8,33 (2,54)	59 (62)	66 (69)
900	8,63 (2,63)	59 (62)	66 (69)
960	8,92 (2,72)	59 (62)	66 (69)
1800	20,60 (6,28)	51 (54)	63 (66)
1900	21,62 (6,59)	50 (53)	62 (65)

NOTES



RLKW12-50CPR

1/2" RADIAFLEX® RLKW Cable, A-series

- Coupling loss as well as longitudinal attenuation of RADIAFLEX® cables are measured by the free space method according to IEC 61196-4.
- Coupling loss values are measured with a radial or parallel (125-800 MHz) orientated dipole antenna.
- The coupling loss values given in brackets are average values of all three spatial orientations (radial, parallel and orthogonal) of dipole antenna.
- Coupling loss values are given with a tolerance of +5 dB and longitudinal loss values with a tolerance of +5%. Note: Measured values below nominal are better. They are not limited by any tolerance-range.
- In case of a conflict of operational and stop band, please contact RFS for further assistance.
- As with any radiating cable, the performance in building or tunnel environments may deviate from figures based on free space method.

;

Related Documents

 **Web URL to CPR resources**
Other Documents

 **WINS Value Proposition** folders
Value Propositions